

1,700nm Wide-Range Light Source

Bland-new Wide-Range Light Source, 1700nm


Main features

Original high luminescence light source;
SLD spontaneous emission followed by
Thulium-based fiber amplifier.




Applications

Light source for componential analysis, OCT,
Organic solvent determination, etc.



C-H bond detection; soluble organic matter into water

Representative data



Specifications

Bandwidth	> 150 nm
	@ -30dB/nm, 1,650-1,800nm

Contact information

Trimatiz Limited

801, La Pacificque B,
4-7-12 Minamiyawata, Ichikawa,
272-0023 Chiba, JAPAN

Tel : +81-47-379-4400
Fax : +81-47-370-0010
www.trimatiz.com

Product specifications and
descriptions in this document
subject to change without notice.